

## FEATURES

- **1.9m cable length:** Provides ample reach for connecting devices to power outlets.
- **IEC C13 to SANS164/1 connectors:** Ensures compatibility with a wide range of equipment and power sources.
- **16 A current rating:** Supports high-power devices, ensuring efficient performance.
- **250 V voltage rating:** Suitable for standard electrical systems, ensuring safety and reliability.
- **Black PVC jacket:** Offers durability and protection against environmental factors.

## RS PRO 1.9m Power Cable, IEC C13 to SANS164/1

RS Stock No: 558-959



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO power cable is designed for reliable electrical connections in various industrial and commercial settings. With a length of 1.9 metres, it offers flexibility and convenience for connecting equipment to power sources. The cable is equipped with an IEC C13 connector on one end and a SANS164/1 connector on the other, making it suitable for use in regions that require these specific plug types.

## General Specifications

Connector Type A	IEC C13
Connector Type B	SANS164/1
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

## Mechanical Specifications

Cable Length	1.9 m
Jacket Material	Polyvinyl Chloride

## Electrical Specifications

Current Rating	16 A
Voltage	250 V

## Approvals

Standards/Approvals	CCCs, CII, CSA, EAC, ENEC 11, ICC, JET, PSE, RCM N10544, SABS, SII, UL
---------------------	--

