



Heat



Welding



Heavy Duty

Heat-resistant industrial gloves, fortified for advanced hand protection in demanding tasks

- **Superior dexterity:** ActivArmr® 43-216 industrial gloves possess a three-dimensional thumb design that optimizes flexibility, ensuring better overall control
- **Enhanced durability and protection:** These durable work gloves are made from high-quality split cowhide leather and feature welted seams, reinforced with Kevlar® thread to guard against heat, flames, sparks and punctures
- **Added protection:** ActivArmr® 43-216 long-cuff gloves provide EN 12477 Type A protection up to the forearms, making them ideal for stick and MIG welding, as well as torch cutting and grinding
- **Elevated comfort:** Greater thermal insulation and extended comfort are also made possible by cotton liners
CAUTION: Do not use in heavy-duty cut applications. These gloves are not liquid-proof and should not be used with chemicals. Keep away from sources of ozone or ignition. Keep out of direct sunlight. Store in a cool and dry place.



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Oil and gas

Applications

- Welding, bonding, riveting
- Metalworking & assembly operations
- Equipment repair & maintenance

Previously known as: ActivArm®Workguard™43-216

Key Features

- **Three-dimensional thumb design:** Enhanced dexterity and control
- **Premium leather and Kevlar®-sewn welted seams:** Durability and comfort
- **Long cuffs with cotton liner:** Increased forearm and wrist protection

Technologies

Kevlar®

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 43-216	Liner Material: Split cowhide leather, Cotton, Kevlar® Cuff Style: Gauntlet	N/A	10	370-415 mm; 14.6-16.3 inches	6 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699