


# PRODUCT SHEET

## 196-...A

### Mat chrome-plated 90° elbowed nose outer circlips pliers

Outer circlip pliers.

reference	nozzle diameter mm	mini. Capacity mm	max. capacity mm	L mm	L"	Weight g
196-10A		8	13	139	5	96
196-13A		12	25	140	5	96
196-17A		19	60	180	7	170
196-21A		40	100	225	9	245
196-28A		85	140	310		445