

DeWalt DCF891N-B1

20V Brushless 1/2" Hog-Ring Wrench

The **DCF891N-B1 18V/20V MAX* XR® Brushless 1/2" Mid-Torque Impact Wrench (Bare Unit)** delivers an exceptional balance of power and compact design. Driven by an advanced brushless motor, it generates an impressive 812 Nm of maximum fastening torque and 1,084 Nm of breakaway torque for stubborn fasteners. Built for maximum control in tight spaces, it features an ultra-short 175mm head length, a lightweight 1.67 kg body, and a 4-mode push-button switch including Precision Wrench™ mode to prevent over-tightening. Complete with a hog ring anvil for quick socket changes and a built-in LED light, it is the ultimate tool for heavy-duty automotive and structural fastening.

Key Features

- Tackle wide range of fastening applications with 812 Nm of max fastening torque and 1084 Nm of max breakaway torque
- Choose the output level based on the job: Control is in your hands with 4 speed settings and a variable speed trigger
- Helps prevent overtightening and fastener run-off with precision wrench™ control

Specifications Table

Specification	Details
Model	DCF891
Socket Drive	1/2"
Voltage	18/20V
Battery	No
Charger	No
Power output	760 W
No Load Speed	0 - 2000 min-1
Impact Rate	0 - 3250 min-1
Precision Wrench™ mode	812 Nm
Low mode	136 Nm
Medium mode	406 Nm
High mode	812 Nm
Max breakaway torque	1084 Nm
LED Light	Yes
Weight (With Out Battery)	1.67 Kg