



Ink Multipack for BradyJet™ J7300 Colour Label Printer (2x CMY, 1x K) Order Reference: P-2CMY1K

Overview

Get better with BradyJet J7300 inks. Designed specifically for the J7300, BradyJet ink cartridges produce vibrant colours, last long and deliver value in every drop.

- CMY Ink Cartridge delivers vibrant, full-colour labels that demand attention
- Works in tandem with K True Black Ink Cartridge to mix more accurate, durable colours
- Ink works with enhanced J7300 label materials topcoat to dry instantly and won't smudge, smear and spot
- Self-contained cartridge drops into printer with a click
- Designed to hold up to 50% more ink for longer use, fewer changeovers and less cartridge waste
- For use with the BradyJet J7300 Colour Label Printer

Specifications

Key Characteristics	Minimum Order Quantity	1
	Article Number	177432
	Order Reference	P-2CMY1K
	Total Qty per Pack	3 Cartridge / Box
	Application(s)	Asset tracking, Barcode labelling, Cold temperature labelling, Facility identification, General identification, Hazard communication identification, Inventory and inspection labelling, Laboratory labelling, Lean and 5S labelling, Pipe and valve marking, Temporary labelling, Warehouse marking
	Quantity	3
	Brand	Brady®
	Trade Name	BradyJet™
	Country of Origin	Philippines
	Country of Origin (SAP)	PH
Dimensions	Size - Width (mm)	121.92 mm
	Size - Height (mm)	71.12 mm
	Size - Depth (mm)	99.06 mm
	Dimensions	121.92 mm (W) x 71.12 mm (H) x 99.06 mm (D)
Material Characteristics	Colour	Cyan, Magenta, Yellow, Black
Printing Specifications	Print Technology	Inkjet
	Smart Cell	Yes
Compatibility	Printer Compatibility	J7300
Compliance	UNSPSC	45101613
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863
	REACH SVHC Status	Part does not contain an SVHC
	REACH Candidate List Date	23 January 2024

Brady Corporation Limited

Wildmere Industrial Estate
Banbury
Oxon
OX16 3JU

Tel: 01295 228200
Fax: 01295 228100
www.bradyeurope.com