

# Comfort Curve Keyboard 3000



eVersion Information	
Product Name	Microsoft® Comfort Curve Keyboard 3000
Product Version	Microsoft Comfort Curve Keyboard 3000 v1.0
Keyboard Version	Microsoft Comfort Curve Keyboard 3000 v1.0
Product Dimensions	
Keyboard Length	18.5 inches (470 millimeters)
Keyboard Width	6.89 inches (175 millimeters)
Keyboard Depth/Height	1.29 inches (33 millimeters)
Keyboard Weight	21.2 ounces (600 grams)
Keyboard Cable Length	60 inches +/- .78 inches (1524 millimeters +/- 20 millimeters)
Compatibility and Localization	
Interface	USB compatible
Operating Systems <sup>1</sup>	<ul style="list-style-type: none"> <li>• Microsoft Windows® 8.1, Windows 8, Windows RT 8.1, Windows RT 8, and Windows 7</li> <li>• Macintosh OS X v10.7-10.9</li> <li>• Android 3.2 and 4.2</li> </ul> <p><sup>1</sup>Advanced functionality not available with all devices and/or operating systems. See compatibility information at: <a href="http://www.microsoft.com/hardware/compatibility">www.microsoft.com/hardware/compatibility</a>.</p>
Top-line System Requirements	Requires a PC that meets the requirements for and has installed one of these operating systems: <ul style="list-style-type: none"> <li>• Windows 8.1, Windows 8, or Windows 7</li> <li>• USB port</li> </ul>
Compatibility Logos	Compatible with Microsoft Windows 8 and Windows RT
Software Localization	No software required
Keyboard Localization	Available language sets will vary by product and sales channel. <b>104 key configuration:</b> Arabic, Chinese (Simplified), Chinese (Traditional), Czech/Slovakian, English (Canada), English (North America), Greek, International English (Euro), International English (India), International English (ROW), Russian, and Thai <b>105 key configuration:</b> All Nordic, English (UK), French (Belgium/Azerty), French (Canada), French (France), German (Germany), German (Switzerland/Luxemburg), Hebrew, Hungarian, Iberian (Portuguese), Italian, Spanish (EURO), Spanish (Latin America), and Turkish <b>106 key configuration:</b> Korean <b>107 key configuration:</b> Brazilian (Portuguese) <b>109 key configuration:</b> Japanese
Product Feature Performance	
QWERTY Key Life	20,000,000 actuations per key
Hot Key Features	Calculator, Play/Pause, Volume +, and Volume -
Hot Key Life	1,000,000 actuations per key
Typing Speed	1000 characters per minute
Storage Temperature & Humidity	-40 °F (-40 °C) to 140 °F (60 °C) at < 5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32 °F (0 °C) to 95 °F (35 °C) at < 5% to 80% relative humidity (non-condensing)
Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
Restriction on Hazardous Substances	This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern.
FCC ID	This device complies with Part 15 of the FCC Rules and Industry Canada ICES-003. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC standards. For home and office use. 1482, Comfort Curve Keyboard 3000.
Agency and Regulatory Marks	<ul style="list-style-type: none"> <li>• ACMA Declaration of Conformity (Australia and New Zealand)</li> <li>• ICES-003 report on file (Canada)</li> <li>• EIP Pollution Control Mark, EPUP (China)</li> <li>• CE Declaration of Conformity (European Union)</li> <li>• WEEE (European Union)</li> <li>• VCCI Certificate (Japan)</li> <li>• KCC Certificate (Korea)</li> <li>• GOST Certificate (Russia)</li> <li>• CITC Letter (Kingdom of Saudi Arabia)</li> <li>• BSMI Certificate (Taiwan)</li> <li>• UkrSEPRO Certificate (Ukraine)</li> <li>• FCC Declaration of Conformity (USA)</li> <li>• UL and cUL Listed Accessory (USA and Canada)</li> <li>• CB Scheme Certificate (International)</li> </ul>
Windows Certification Kit (WCK)	ID: 1608625 (32-bit) and 1608628 (64-bit) Microsoft Windows 8.1

Results stated herein are based on internal Microsoft testing. Individual results and performance may vary. Any device images shown are not actual size. This document is provided for informational purposes only and is subject to change without notice. Microsoft makes no warranty, express or implied, with this document or the information contained herein. Review any public use or publications of any data herein with your local legal counsel.