

**WHEEL D 200X50/60 NYLON BEARING SWIVEL FORK  
M22 + BRAKE**



**Wheel series D**

Wheels with black rubber ring on thermoplastic core, available with roller bearings or nylon friction bearings.  
The wheel is fitted with bushes.



**Castor series M22**

M22 series, Medium-light pressed steel fork assemblies; swivel version has double ball raceways. Zincplated.  
Trailing foot brake - total stop.



**Technical data**

Wheel diameter	D	200 mm
Tyre width	E	50,0 mm
Bore diameter	d	20 mm
Weight article		2,990 kg
Hub width	L	60 mm
Overall height	H	240 mm
Top plate outer dimensions	AxB	135x110 mm
Bolt hole spacing	axb	105x75 mm
Bolt hole spacing	axb	105x80 mm
Fixing bolt diameter	g	M10
Offset	F	59 mm
Fork width	U	60 mm
Load Capacity		205 kg

**Related Articles**

Spare part wheel: [13136](#)

Basic version: [13936](#)

Version with thread-guards: [13936PF](#)

Version with footguard: [13936PP](#)

Version with trailing brake and thread-guards: [13936FRPF](#)

Version with trailing brake and footguard: [13936FRPP](#)

**GENERAL INFORMATION / RECOMMENDATIONS AND WARNINGS**

The cited text and the complete catalogue in their most up-dated versions are available in the OEM's website page [www.lagspa.it/downloads](http://www.lagspa.it/downloads). The dimensions, descriptions, specifications and illustrations herein are indicative and subject to variations without notice. The fact that products are illustrated herein does not necessarily imply they are available from stock nor does it place us under any obligation to supply them.

Tests carried out refer to the original products with original accessories: the replacement of one of the components with others of different manufacture might prevent the same results from being achieved and will automatically invalidate any guarantee. Please contact our technical service concerning any special application.