



Socket Outlets

Description

A range of 1g and 2g socket outlets with either single or double switches, or unswitched.

This uniquely shaped range is easy to install, with coloured terminals, clear white terminal markings and is supplied in individual protective bags.

Features

- unique slim profile with curved top and bottom edges
- concave rockers
- only one size 4mm screwdriver needed
- clear white markings
- colour coded terminals
- top facing terminal screws
- DP switch versions
- 2 earth terminals on DP sockets
- terminals have large lead-ins
- 25 year guarantee

Range	
1g unswitched	S1206
2g unswitched	S1208
1g recessed SP switch	S1207R
1g standard SP switch	S1207S
2g recessed SP switch	S1209R
2g standard SP switch	S1209S
1g standard DP switch	S1207SDP
1g standard DP switch & neon	S1207DPP
2g standard DP switch	S1209SDP
2g standard DP switch & neon	S1209DPP
2g standard outboard DP	S1293
switch	

Technical Specification

voltage rating	250Vac
current Rating	13A per outlet
contact gap	3mm

no user serviceable parts

Back Boxes

minimum recommended depth

	flush	dry lining	surface
	25mm	35mm	25mm
1g	DB162	DB2540	V1221
2g	DB163	DB2541	V1223

Standards

• BS 1363 Part 2 : 1995

Terminal Capacity

_	2.5mm ²	4mm ²	6mm ²	10mm ²
L & N	4	3	2	1

DETA

Kingsway House, Laporte Way Luton, Beds LU4 8RJ Tel. +44 1582 544 500 Fax: +44 1582 544 501 Technical Helpline +44 1582 544 548