

E-Mail: info@harrisonwipes.co.uk Website: www.harrisonwipes.co.uk



HARRISON WIPES				Item Name : EDW 35gsm				
Composition : 100% Polyester				Appearance : 22 Mesh, Wavy Printing				
Lot No : N/A				Test Date: 27 th March 2019				
Test Items		Unit	Standard	Roll Average			Test No	Test Method
				Avg.	Min.	Max.		
Basis Weight		g/m ²	35 ± 3.3	34.8	---	---	8	EDANA 40.3-90 (25*20 cm ²)
Thickness		mm	0.23 ± 0.03	0.23	---	---	8	FZ/T 60004-91 20gf/cm ² , 15.2cm ²
Tensile Strength at Break	MD	Kg/50 mm	3.0 ↑	13.4	---	---	4	EDANA 20.2-89 Test Speed : 300mm/min Grip Distance : 100mm Specimen Width : 50mm
	CD		1.0↑	1.3	---	---	4	
Elongation at Break	MD	%	60 ↓	15.6	---	---	4	
	CD		190 ↓	174.7	---	---	4	
Absorption Capacity		%	350 ↑	620	---	---	4	ISO 9073 - 6:2000
Speed of Absorbability		cm/30s	3.0 ↑	4.0	---	---	4	Corporation Standard
Remarks:								