

Abrasion-resistant chemical gloves with heightened grip, perfect for indoor application

- **Enhanced grip:** AlphaTec® 58-530W chemical gloves' ANSELL GRIP™ coating means less force is required when handling wet or oily components
- **Elevated comfort:** Their white nylon inner liner enhances comfort and offers excellent durability
- **Advanced defenses:** A bonded construction, whereby their coating polymer doesn't penetrate the liner in manufacture, guarantees EN 374 Type A chemical protection
- **Improved durability:** These AlphaTec® gloves also achieve EN level 3 and ANSI level 5 abrasion resistance levels
- **Specialized protection:** In addition, they offer EN 407 heat resistance, for improved workplace safety
- **Augmented dexterity:** AlphaTec® 58-530W industrial gloves' light 13-gauge design makes them more dexterous, for maneuverable hand protection

Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Oil and gas

Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Changing tools and dies
- Handling application & cleaning tools
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process



AlphaTec®

ADVANCED CHEMICAL PROTECTION

58-530W

Unique combination of grip and chemical resistance

Key Features

- **ANSELL GRIP™ Technology:** Less force needed to grip wet or oily parts
- **White nylon liner:** Safety gloves with enhanced comfort and durability
- **Bonded construction:** Zero liner penetration, heightened dexterity

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-530W	Nylon, Nitrile, ANSELL GRIP™	7, 8, 9, 10, 11	290 / 11.4	Grey	<ul style="list-style-type: none"> • 6 pairs/polybag; 12 polybags/carton • Vend pack variant ,1 pair per bag,72 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

