



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2234157-1
DIE SET PCON 12-2P F 16MM2


Customers Also Bought



TE Part #1623789-9
SQM7 22R 5% (WIRE)



TE Part #2413297-1
SHIELDING SLEEVE,180DEG



TE Part #W016068
O-RING 102X5 EPDM 60



TE Part #1719826-7
SINGLE WIRE SEAL,8MM HV



TE Part #2141612-6
RADIAL SEAL,25X43,CABLE SEAL, BL



TE Part #2141613-6
CARRIER,SEAL,BL



TE Part #2141614-2
COVER, CABLE SEAL



TE Part #2141614-6
COVER,CABLE SEAL



TE Part #2141784-2
2POS,RING TONGUE,HSG,ASSY,
SEALED



TE Part #2311753-2
2POS,PCON12,REC HSG ASSY,
180DEG,COD B

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2310221-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2310221-1_A.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_CVM_2310221-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English