



iM3075

Storm

Transport Case

The Peli™ Storm Case™ has the same legendary DNA as our Peli Protector Case, with one primary difference: A unique Press and Pull latch that locks automatically, but open with a light touch. Guaranteed for life, the Peli Storm case is made in the USA and engineered using the finest components.

- Seven Press & Pull Latches
- Two Padlockable Hasps
- Two Double-layered, Soft-grip Handles
- In-line Wheels
- Powerful Hinges
- O-ring seal



CONFIGURATIONS



iM3075
Standard



iM3075-X0000
No Foam



iM3075-X0002
With Padded Dividers



iM3075-X0001
With Foam

DIMENSIONS

Interior (L×W×D)	29.80 x 20.80" x 17.80 (75.7 x 52.8 x 45.2 cm)
Exterior (L×W×D)	33.30 x 24.40" x 19.30 (84.6 x 62 x 49 cm)
Lid Depth	4.00" (10.2 cm)
Bottom Depth	13.75" (34.9 cm)
Total Depth	17.75" (45.1 cm)
Int Volume	6.38 ft ³ (0.181 m ³)
Padlock Hole Diameter	0.35" (0.9 cm)

MATERIALS

Body	Injection Molded HPX™ high performance resin
Latch	Valox - Polybutylene Terephthalate (PBT)
Latch (Alt)	Xenoy - Polyester/Polycarbonate blend
O-Ring	EPDM
Pins	Stainless Steel
Pins (Alt)	Aluminum
Foam	1.3/1.35 polyester
Purge Body	Valox - Polybutylene Terephthalate (PBT)
Purge Body (Alt)	Xenoy - Polyester/Polycarbonate blend
Purge Vent	Gortex membrane

COLOURS

 Black	 OD Green
---	--

WEIGHT

Weight With Foam	45.00 lbs (20.4 kg)
Weight Empty	31.50 lbs (14.3 kg)
Buoyancy	388.20 lbs (176.1 kg)
Master Pack Weight	37.00 lbs (16.8 kg)

TEMPERATURE

Minimum Temperature	-20°F (-28.9 °C)
Maximum Temperature	140°F (60 °C)



CERTIFICATIONS

IP67	
-------------	--

OTHER

Extendable Handle	yes
Master Pack	1
Military	yes

ACCESSORIES

				
iM3075-FOAM 7 pc. Replacement Foam Set	iM3075-DIV Padded Divider Set	iM-LIDSTAY Lid Stay	iM3075-UTILITYORG Utility Organizer	iM3075-M4-BEZEL-L Lid Bezel Kit (Metric)
				
iM3075-MBEZ-B Base Bezel Kit (Metric)	1506TSA TSA Lock	1500D Desiccant Silica Gel		