

# 12vdc Input CC 350mA output 2W DC-DC LED Driver Wired 3-10vdc



## Features:

- Suitable for 12V & 24V LEDs lighting application.
- Fly leads 20AWG 15cm for rapid connection.
- Waterproof packaging:IP65 for dry and wet location
- Tc Point measured, Max case temperature: 70°C
- Protections: Short-Circuit



ENGLISH

Specifications	
RS Part Number	1766765
Voltage Range (VAC)	12Vdc
Voltage Range (VDC)	3-10Vdc
Rated Current Range	350mA+10%
Rated Power	1-2W
Efficiency	74%
Ambient Temp	-10°C~+40°C full load
Operating Humidity	20% ~ 95% RH non-condensing.
Storage Temp/ Humidity	-20 ~ +80°C / 10% ~ 95% RH
Safety Standards	CE
Cord code/ Cord Colour	Primary: 1007/#20 15cm L:Brown , N:Blue Secondary: 1007/#20 15cm +:red -:black