



tesa[®] PRO 66714 Mounting Slim

Product Information



Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Backing	PE foam	• Color	white
• Type of adhesive	tackified acrylic	• Color of liner	brown
• Total thickness	1000 µm		

Properties/Performance Values

• Elongation at break	180 %	• Static shear resistance at 40°C	good
• Tensile strength	10 N/cm	• Static shear resistance at 70°C	very good
• Ageing resistance (UV)	very good	• Tack	good
• Humidity resistance	very good	• Temperature resistance long term	80 °C
• Softener resistance	medium	• Temperature resistance short term	80 °C
• Static shear resistance at 23°C	good		

Adhesion to Values

• ABS (initial)	8 N/cm	• PET (after 14 days)	13.5 N/cm
• ABS (after 14 days)	13.5 N/cm	• PP (initial)	1.2 N/cm
• Aluminium (initial)	8 N/cm	• PP (after 14 days)	1.2 N/cm
• Aluminium (after 14 days)	13.5 N/cm	• PS (initial)	8 N/cm
• PC (initial)	8 N/cm	• PS (after 14 days)	8 N/cm
• PC (after 14 days)	13.5 N/cm	• PVC (initial)	13.5 N/cm
• PE (initial)	0.9 N/cm	• PVC (after 14 days)	13.5 N/cm
• PE (after 14 days)	0.9 N/cm	• Steel (initial)	13.5 N/cm
• PET (initial)	6 N/cm	• Steel (after 14 days)	13.5 N/cm



tesa[®] PRO 66714 Mounting Slim

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?mp=66714>