

Previously known as: Sensilite®



Multi Purpose



Light Duty

Fingertip-coated light-duty work gloves, providing protection against electrostatic discharge

- **Specialized protection:** HyFlex® 48-135 light-duty industrial gloves are designed to resist electrostatic discharge (ESD)*, ensuring product protection
- **Improved tactility:** Developed with polyurethane coating around the fingertips, these HyFlex® gloves grant wearers excellent levels of flexibility and tactility, perfect for precision handling
- **Elevated comfort:** Due to their seamless construction and varied sizing options, HyFlex® 48-135 ESD-resistant safety gloves provide a comfortable, optimized fit
 - *EN 1149-1: Surface resistivity (Ω): 1.93×10^{10}
 - EN 1149-2: Volume resistance (Ω): 4.79×10^7
 - EN 1149-3: Charge decay T50 less than 0.01 seconds



Previously known as: Sensilite®

Key Features

- **Electrostatic discharge protection:** Safeguarding product integrity
- **Polyurethane fingertip coating:** Ample flexibility and tactility
- **Seamless construction, varying sizes:** Optimal fit, optimal comfort

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 48-135	Finishing: Fingertip Coated Coating Material: Polyurethane Liner Material: Nylon Cuff Style: Knitwrist	15	6, 7, 8, 9, 10, 11	190-240 mm; 7.48-9.45 inches	White	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.