

FR716 - PW3 FR Modaflame Class 1

Sweatshirt

Collection: PW3

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Knit HV: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre

Outer Carton: 24



Product information

Ideal for workers exposed to heat in their working environment. Features on this garment include, round neck, ribbed collar and cuffs, making it comfortable and easy to wear. Class 1 high visibility gives the wearer added protection.

PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 9.2 CAL/CM², ATPV 15 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN ISO 20471 Class 1

ASTM F1959/F1959M-12 (ATPV=16 Cal/CM² (HAF=86%))

Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- High cotton content for superior comfort
- Ribbed cuffs for added comfort
- Ribbed hem for a comfortable fit
- Outstanding colour fastness and shrinkage results
- Crew neck
- Anti-static
- 40+ UPF rated fabric to block 98% of UV rays
- CE certified
- CE-CAT III



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

FR716 - PW3 FR Modaflake Class 1 Sweatshirt

Commodity Code: 6110309900

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/12776-05/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR716YBRS	Yellow/Black	60.0	40.0	40.0	0.9990	0.0960	5036108405237	15036108890207
FR716YBRM	Yellow/Black	60.0	40.0	40.0	0.6980	0.0960	5036108405220	15036108890191
FR716YBRL	Yellow/Black	60.0	40.0	40.0	0.9990	0.0960	5036108405213	15036108890184
FR716YBRXL	Yellow/Black	60.0	40.0	40.0	0.9990	0.0960	5036108405244	15036108890214
FR716YBRXXL	Yellow/Black	60.0	40.0	40.0	0.7870	0.0960	5036108405251	15036108890221
FR716YBRXXXL	Yellow/Black	60.0	40.0	40.0	0.9990	0.0960	5036108405268	15036108890238