

LED lamp 025 Magnetic fixing 100-240 V AC



Model		
product brand name	SIVACON	
product designation	LED light	
design of the product	Without screw fixing	
type of light source	LED	
General technical data		
consumed active power / of the light source	5 W	
Protection class		
protection class IP	IP20	
Product details		
product component		
• ON/OFF switch	Yes	
• light sensor	No	
• socket outlet	No	
product feature / magnetic	Yes	
Connections		
type of electrical connection / for through-wiring	Plug-in connection	
Mechanical Design		
height	34 mm	
width	32 mm	
depth	34 mm	
length	351 mm	
net weight	0.2 kg	
material	plastic	
Certificates		
reference code		
• acc. to DIN EN 61346-2	E	
• acc. to IEC 81346-2	E	
General Product Approval	Declaration of Conformity	Dangerous Good



[Transport Information](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=8MR2200-1A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2200-1A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR2200-1A

Tender specifications

<http://www.siemens.com/specifications>

