



DCS310N

10.8V XR Li-Ion Compact Recip Saw - Bare Unit

Selling Proposition

- Adjustable 3 position pivoting handle provides user with flexibility to work in confined spaces.
- Powerful 10.8V reciprocating saw for small to medium applications
- Compact, lightweight design
- Ergonomic handle and rubber overmold provide ultimate end user comfort
- Lever action keyless blade clamp for quick and easy blade change
- Parabolic switch profile allows greater control of application

Standard Equipment

- Battery and charger sold separately

Warranty Specifications

- 30 Tage-Geld-zurück-Garantie
- 3 year limited warranty
- 1 Year Free Service Contract

| Specifications | |
|---------------------|-------------|
| Battery chemistry | XR Li-Ion |
| Voltage | 10.8 V |
| Kapazität | N/A Ah |
| Abgabeleistung | 140 Watt |
| No Load Stroke Rate | 0-2,700 spm |
| Stroke Length | 14 mm |
| ´Gewicht | 1.2 kg |
| Länge | 255 mm |