

Datasheet

RS Pro D-sub Interface Module, DIN Rail Mount, Female, 15 Pole, 125 V ac/dc, 1.5A, 51mm

RS Stock No: **665-9683**



Product Details

RS Pro D-sub interface module has a female plug with 15 contacts to supports 14 to 22 AWG D-sub miniature connection into screw clamp terminals. This module features a compact 47 mm profile with simple assembly. It has 1.5 A of current rating per pin. The module has an insulating stripping length and screw/tension spring of 6 to 7 mm. It is the best alternative to pure individual wire approach. It measures 47 x 51 mm.

Features and Benefits

- Interconnect D-Subminiature into screw-clamp terminals
- D-Sub according to MIL-C-24308/DIN41652
- Compact 47 mm profile
- Rail mount on DIN-rail TS35
- 1.5 A current rating per pin
- Stripping length, screw/tension spring of 6 to 7 mm
- Alternative to pure individual wire approach

**Specifications:**

| | |
|-------------------------------|----------------------------|
| Cable CSA | 0.2 to 2.5 mm ² |
| Connector Type | D-Sub |
| Current Rating | 1.5 A |
| Depth | 47 mm |
| Dimensions | 51 x 61 x 47 mm |
| Gender | Female |
| Length | 51 mm |
| Maximum Operating Temperature | +50°C |
| Minimum Operating Temperature | -20°C |
| Mounting Type | DIN Rail Mount |
| Number of Contacts | 15 |
| Test Proof Voltage | 0.6 kV |
| Voltage Rating | 125 V ac/dc |
| Width | 61 mm |
| Wire Size | 22 to 14 AWG |
| Number of Poles | 15 |