

PVA-coated protective gloves, delivering superior protection against chemical hazards

- **Optimized protection:** AlphaTec® 15-554 liquid- and chemical-resistant gloves are among the only ones suitable for handling strong organic chemicals, remaining virtually inert in aromatic and chlorinated solvents
- **Enhanced ergonomics:** These high-dexterity work gloves are shaped to natural hand contours, featuring precurved fingers and a winged thumb design that promotes natural mobility and tactile sensitivity, reducing hand fatigue
- **Elevated comfort:** With their soft, two-piece knitted liner, AlphaTec® 15-554 industrial gloves also cushion the hand and absorb perspiration, keeping hands dry and cool



Industries

- Life Sciences
- Chemical

Applications

- Maintaining lab furniture and equipment
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process
- Unexpected leakages spills or other releases

Previously known as: PVATM 15-554

Key Features

- **PVA coating:** Advanced resistance to aromatic and chlorinated solvents
- **Anatomical design:** For secure, form-fitting hand protection gloves
- **Soft two-piece knit liner:** Reduced perspiration, enhanced comfort

Please note, whilst PVA provides excellent protection against solvents, PVA is water soluble.

Contact with water or use in high humidity environments will greatly decrease chemical protection



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 15-554	Liner Material: Interlock cotton Coating Material: Polyvinylalcohol	9, 10	355 / 14	Red	• 1 pair in a bag; 12 bags in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.