

FEATURES

- **Non-Releasable Design:** Provides a secure and permanent fastening solution.
- **Nylon Material:** Offers durability and resistance to wear and tear.
- **UL 94 V-0 Fire Behaviour:** Ensures high flame retardancy for safety in various environments.
- **Tensile Strength of 22 kg:** Capable of handling substantial loads without breaking.
- **Maximum Bundle Diameter of 83 mm:** Accommodates a wide range of cable sizes.
- **RoHS Compliant:** Meets environmental and safety standards.

RS PRO 300mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-038



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a robust 300mm nylon cable tie designed for secure and permanent bundling of cables and wires. Ideal for both industrial and domestic applications, this non-releasable cable tie ensures a reliable hold, making it a dependable choice for organising and managing cables efficiently.

General Specifications

Colour	White
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	22 kg

Protection Category

Fire Behaviour	UL 94 V-0
UV Resistant	No

Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	83 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	RoHS, UL94V-0
---------------------	---------------