

STANLEY

FMHT70250-0

STANLEY® FATMAX® 2-in-1 Multi Tacker

The STANLEY® FATMAX® 2-in-1 Multi Tacker is perfect for multiple professional applications including fixing drywall beads and scrim to plasterboard, securing carpets, fencing and roof sheeting. It features an anti-jam mechanism for continuous use and reliable operation, as well as a high and low power setting to control the intensity of the staple application. Takes Type-G Staples and Type-J Brad Pins.



FEATURES & BENEFITS

EASY SQUEEZE TECHNOLOGY: For reduced fatigue and added driving power into materials.

ANTI-JAM MECHANISM: Prevents fasteners jamming, for continuous use and reliable operation.

HIGH-LOW POWER SETTING: Controls intensity of staple application when working on a variety of hard and soft materials.

STAPLE RELOAD: Easy to reload staple gun.

STAPLE WINDOW: Provides clear visibility to determine when staple reload is required.

INTEGRATED HANDLE LOCK: For safe storage and transportation.

BELT CLIP: For convenient storage whilst working and easy transportation.

SOFT GRIP HANDLE: For added comfort.

ALUMINIUM CONSTRUCTION: For long-lasting durability.

COMPATIBLE FASTENINGS: Fires STANLEY® Type-G staples in 6mm - 14mm and STANLEY® Type-J Headed Brad Pins in 12mm - 15mm.

STAPLES NOT INCLUDED.



STANLEY

FEATURES & BENEFITS



SUITABLE FOR A VARIETY OF PROFESSIONAL APPLICATIONS

Ideal for fixing drywall beads and scrim to plasterboard, securing carpets, fencing and roof sheeting, plus more.



HIGH-LOW POWER SETTING

Controls intensity of staple application when working on a variety of hard and soft materials.



STAPLE RELOAD

Easy to reload staple gun.



INTEGRATED HANDLE LOCK

For safe storage and transportation.



SOFT GRIP HANDLE

For added comfort.



COMPATIBLE FASTENINGS

Fires STANLEY® Type-G staples in 6mm - 14mm and STANLEY® Type-J Headed Brad Pins in 12mm - 15mm.