
RS PRO Non-Metallic Blind Flange Lockout - Small (Pipe Size 3-3/4 - 10-3/4)

RS Stock No.: 0802207



Features

- Adjustable blind flange lockout device.
- Prevents removal of pipe blinds during maintenance.
- Conceals and locks access to flange nuts.
- Durable high-impact plastic construction.
- Accepts padlocks up to 8 mm shackle diameter.
- Suitable for –20°C to +60°C environments.
- Ideal for oil & gas, petrochemical, and process industries.

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Prevents Unintentional Removal of Pipe Blinds*** *- Specifically engineered to secure blind flanges and prevent unauthorised or accidental removal during maintenance or shutdown procedures.*
- ***Adjustable Secure-Fit Design*** *- Adjustable configuration ensures a tight and secure fit over flange nuts, fully concealing and restricting access to the fastening hardware.*
- ***Conceals & Locks Flange Nuts*** *- Encloses the nuts holding the blind flange in place, preventing tampering and maintaining isolation integrity.*
- ***High-Impact Durable Plastic Construction*** *- Manufactured from strong, impact-resistant plastic designed to withstand harsh industrial environments.*
- ***Wide Operating Temperature Range*** *- Suitable for use in temperatures from* ***-20°C to +60°C****, making it ideal for both indoor and outdoor applications.*
- ***Padlock Compatible*** *- Accommodates padlocks with shackle diameters up to* ***8 mm****, allowing secure lockout control.*

General Specifications

Type	Blind Flange Lockout
Material	PVC
Colour	Red
Padlock holes	01
Package	PE-LD

Mechanical Specifications

Fits Nut Diameter (Class 150)	0.75" to 0.88" (19.05mm – 22.35mm)
Fits Nut Diameter (Class 300)	0.75" to 1.00" (19.05mm –25.4mm)
Pipe Flange Width Range	3-3/4" - 10-3/4" (95.3mm - 274.6mm)
Length	229mm
Width	46mm
Height	103mm
Weight	100 Grams

Operation Environment Specifications

Withstand temperature	-20°C to +60°C


DANGER
LOCKED OUT
DO NOT REMOVE
LOCK OUT HERE
DANGER
DO NOT OPERATE