



PRODUCT-DETAILS

# E 93N/50s

## Fuse disconnecter



| 概要信息        |                                                                                                                                                              |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 产品型号        | E 93N/50s                                                                                                                                                    |
| 产品ID        | 2CSM256302R1801                                                                                                                                              |
| 欧洲商品编号(EAN) | 8012542563020                                                                                                                                                |
| 目录说明        | Fuse disconnecter                                                                                                                                            |
| 详细描述        | E 90 50/125 fuse holders are appropriate to protect against overloads and short circuits. They are designed for use with cylindrical fuses from 50 to 125 A. |

| 技术参数                     |                                            |
|--------------------------|--------------------------------------------|
| 适用于                      | E 90                                       |
| 适用产品系列                   | Fuse holders                               |
| 额定电压 (U <sub>r</sub> )   | acc. To IEC 690 V<br>acc. To UL 690 V      |
| 额定工作电压                   | AC-20B 690 V                               |
| 额定绝缘电压 (U <sub>i</sub> ) | 1 kV                                       |
| 额定频率 (f)                 | 50/60 Hz                                   |
| 功率损耗                     | at Rated Operating Conditions per Pole 5 W |
| 保护极数                     | 3                                          |

|                            |                                                                                       |
|----------------------------|---------------------------------------------------------------------------------------|
| 极数                         | 4P                                                                                    |
| 中性端子位置                     | Right                                                                                 |
| 拧紧力矩                       | 3...3.5 N·m                                                                           |
| 利用类别                       | Connecting and disconnecting under no-load conditions - occasional actuation (AC-20B) |
| Lock Type                  | Padlockable                                                                           |
| 安装类型                       | DIN-Rail                                                                              |
| 封口类型                       | Sealing Wire                                                                          |
| Material of Conductor      | Copper                                                                                |
| 提供的选项                      | With LED                                                                              |
| 推荐的螺丝刀                     | Pozidriv 2                                                                            |
| 连接容量                       | Rigid 2.5...25 mm <sup>2</sup><br>Rigid Stranded 2.5...35 mm <sup>2</sup>             |
| 熔断器规格                      | 14x51 mm<br>max. 90% with temp. +20 °C 50% with max. temp. +40 °C                     |
| 额定工作电流AC (I <sub>e</sub> ) | 50 A                                                                                  |

### Material Compliance

|                                             |                                                                        |
|---------------------------------------------|------------------------------------------------------------------------|
| RoHS信息                                      | 2CSC444009D2701                                                        |
| RoHS状态                                      | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |
| RoHS日期                                      | 01/01/2014 0.00.00                                                     |
| REACH Declaration                           | 9AKK108467A9482                                                        |
| REACH Information                           | True - contains substances > 0.1 mass percentage                       |
| REACH Date                                  | 20240429                                                               |
| Conflict Minerals Reporting Template (CMRT) | 9AKK108468A3363                                                        |

### 环境条件

|                         |                                                       |
|-------------------------|-------------------------------------------------------|
| 周围环境温度                  | Storage -5...+40 °C<br>Storage Operation -25...+70 °C |
| 防护等级                    | IP20                                                  |
| 耐振动符合IEC 60068-2-6标准    | 1 mm 2 ... 13 Hz                                      |
| 抗机械冲击符合IEC 60068-2-27标准 | 15g 18 shocks 11 ms                                   |
| 环境信息                    | See RoHS Information                                  |

### 尺寸

|                      |          |
|----------------------|----------|
| 宽度(模块化垫片数)           | 6        |
| 产品净宽                 | 106.8 mm |
| 产品净高                 | 96.5 mm  |
| 产品净深                 | 73.26 mm |
| 产品净重                 | 380 g    |
| 内深 (t <sub>2</sub> ) | 73.26 mm |

### 订货信息

|         |             |
|---------|-------------|
| 1级包装单元  | box 1 piece |
| 1级包装 总重 | 0.38 kg     |

E-Number (Norway)

1416159

认证及声明（文件编码）

|            |                                   |
|------------|-----------------------------------|
| BV认证       | 9AKK108467A0329                   |
| CCC认证      | 9AKK108467A0342                   |
| 符合性声明 - CE | 2CSC444009D2701                   |
| KRS认证      | 9AKK108467A0338                   |
| LR认证       | 9AKK108467A0332                   |
| RINA认证     | 9AKK107992A0866                   |
| UL认证       | 9AKK107992A1040                   |
| 认证机构       | BV, Korean register, CCC, EAC, UL |

Installation

|        |                    |
|--------|--------------------|
| 说明书和手册 | No document needed |
|--------|--------------------|

Popular Downloads

|           |                 |
|-----------|-----------------|
| 数据手册，技术资料 | 2CSC444002B0204 |
|-----------|-----------------|

分类

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| ETIM 8             | EC002705 - Holder for cylindrical fuse                     |
| ETIM 9             | EC002705 - Holder for cylindrical fuse                     |
| WEEE 类别            | 5. Small Equipment (No External Dimension More Than 50 cm) |
| WEEE B2C / B2B     | Business To Consumer                                       |
| CN8                | 85361050                                                   |
| UNSPSC             | 39121624                                                   |
| e级                 | V11.0 : 27142121                                           |
| IDEA 粒度分类代码 (IGCC) | 4974 >> Holder for cylindrical fuse                        |
| 对象分类代码             | F                                                          |

Accessories

| Identifier      | Description | Type        | Quantity | Unit Of Measure |
|-----------------|-------------|-------------|----------|-----------------|
| 2CSM277523R1801 | Fuse link   | E 9F14 GG2  | 1        | piece           |
| 2CSM277303R1801 | Fuse link   | E 9F14 GG4  | 1        | piece           |
| 2CSM277083R1801 | Fuse link   | E 9F14 GG6  | 1        | piece           |
| 2CSM291003R1801 | Fuse link   | E 9F14 GG8  | 1        | piece           |
| 2CSM290983R1801 | Fuse link   | E 9F14 GG10 | 1        | piece           |
| 2CSM290963R1801 | Fuse link   | E 9F14 GG12 | 1        | piece           |
| 2CSM258783R1801 | Fuse link   | E 9F14 GG16 | 1        | piece           |
| 2CSM257603R1801 | Fuse link   | E 9F14 GG20 | 1        | piece           |
| 2CSM256423R1801 | Fuse link   | E 9F14 GG25 | 1        | piece           |
| 2CSM258693R1801 | Fuse link   | E 9F14 GG32 | 1        | piece           |
| 2CSM257513R1801 | Fuse link   | E 9F14 GG40 | 1        | piece           |
| 2CSM256333R1801 | Fuse link   | E 9F14 GG50 | 1        | piece           |

分类

低压产品及系统 → 线路保护产品 → Protection and Safety Devices → Cylindrical Fuse Holders and Fuse Switch Disconnectors



360°