

Features

- Crocodile Clips
- Large Battery Clip with Insulators installed
- Jaw Opens 1.5" (38mm) Max
- Copper Plated Steel
- Rating: 200 Amps

RS PRO Crocodile Clips, Copper-Plated Steel Contact, 200A, Red

RS Stock No.: 0205392



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Crocodile Clips



Product Description

- General purpose range of battery clips from RS provide the user with a robust and reliable product. Can be attached via crimp or solder methods, and comes equipped with a variety of coloured insulators
- Copper plated steel rated at 200A
- RS Electric Heavy Duty, General Purpose, Crocodile and Alligator Clips
- A concise offering of steel and copper alligator and crocodile clips from RS suitable for applications including grounding clips, test meters clips, battery terminal connection and many others that require a durable and hardwearing alligator or crocodile clip.

General Specifications

Material	Clip – Copper Plated Steel Insulators – Flexible PVC
Product Name	Heavy Duty Clip
Type	Automotive clip Heavy Duty Clip for Battery and Test Work
Insulated	Yes
Connection Type	Connection can be made by crimp or solder with up to 1 AWG Wire

Commented [波幸1]:

Electrical Specifications

Current rating	200A
----------------	------

Mechanical Specifications

Jaw Opening (±10%)	Jaw Opens 1.5" (38mm) Max
Contact Material	Copper Plated Steel
Insulation Material	Red Flexible PVC
Dimensions (±10%)	Length 6.0" (153 mm), Width =0.97" (24.7mm)

Approvals

Standards Met	RoHS Compliant
---------------	----------------

Crocodile Clips



Declarations	Reach
--------------	-------

PRODUCT DIMENSION DRAWING AND ADDITIONAL INFORMATION