

Features

- D25 Male
- D25 Female
- Port Saver

RS PRO D25 (M) to D25 (F) Port Saver

RS Stock No.: 0839424



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

D25 Male to female port saver, these are classed as port savers as they have a straight through configuration and do not convert the port in to another type. These take the wear and tear of continuous insertion and removal of cables.

General Specifications


Accessory Type	Adapter
Connector 1	D25
Connector 1 Gender	Male
Connector 2	D25
Connector 2 Gender	Female
Colour	Yellow / Silver
Application	Communications ports, Network ports, Computer video output, Game controller ports

Approvals

Standards Met	CE UKCA REACH ROHS
---------------	--------------------

Other Products in This Range

Stock No.	Brand	Type	Connector A	Connector B
0839476	RS PRO	Adapter	D25 (M)	D25 (M)
0839477	RS PRO	Adapter	D25 (F)	D25 (F)
AD-111	RS PRO	Adapter	D15 (M)	D15 (M)
AD-112	RS PRO	Adapter	D15 (F)	D15 (F)
AD-401	RS PRO	Serial Adapter	D9 (F)	D25 (M)
AD-402	RS PRO	Serial Adapter	D9 (F)	D25 (F)
AD-403	RS PRO	Serial Adapter	D9 (M)	to D25 (M)
AD-404	RS PRO	Serial Adapter	D9 (M)	D25 (F)
0839422	RS PRO	VGA Adapter	D9 (M)	HD15 (F)
0839423	RS PRO	VGA Adapter	D9 (F)	HD15 (M)
AD-425	RS PRO	VGA Leaded Adapter	D9 (F)	HD15 (M)
AD-426	RS PRO	VGA Leaded Adapter	D9 (M)	HD15 (F)
0839424	RS PRO	Port Saver	D25 (M)	D25 (F)
0839425	RS PRO	Null Modem Adapter	D25 (M)	D25 (F)
0839427	RS PRO	Port Saver	D9 (M)	D9 (F)
AD-666	RS PRO	Port Saver	HD15 (M)	HD15 (F)



SPECIFICATION:

1. VOLTAGE RATING: 300V AG(rms).
2. CURRENT RATING: 5 AMP CONTINUOUS
3. DIELECTRIC STRENGTH 1000VAG
4. CONTACT RESISTANCE: 10m Ohm min