

PRODUCT DATASHEETP CLAS B 40 4.5 W/2700K E14

PARATHOM Retrofit CLASSIC B DIM | Dimmable LED lamps, classic bulb shape



AREAS OF APPLICATION

- Domestic applications
- General illumination
- Outdoor use in outdoor luminaires only (minimum IP65)
- Perfect for decorative installations

PRODUCT BENEFITS

- Design, dimensions, luminous flux comparable to an incandescent lamp
- Very low energy consumption
- Robust against vibrations
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs
- Lamps with innovative LED "filament" technology

PRODUCT FEATURES

- Professional LED lamps for line voltage
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Mercury-free lamps
- Lifetime: up to 15,000 h
- Beam angle: up to 300°



TECHNICAL DATA

Electrical data

Rated wattage	4.50 W
Nominal wattage	4.50 W
Nominal voltage	220240 V
Max. lamp no. on circuit break. 10 A (B)	460
Max. lamp no. on circuit break. 16 A (B)	736
Operating frequency	5060 Hz
Power factor λ	> 0.70
Claimed equiv. conventional lamp power	40 W


Photometrical data

Nominal luminous flux	470 lm
Rated luminous flux	470 lm
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Luminous flux	470 lm
Color rendering index Ra	≥80
Standard deviation of color matching	≤6 sdcm
Rated color temperature	2700 K

Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	97.0 mm
Diameter	35.0 mm

Outer bulb	B35
Length	97.0 mm

Temperatures & operating conditions

Ambient temperature range	-20+40 °C
Maximum temperature at tc test point	50 °C

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000

Additional product data

Base (standard designation)	E14		
Mercury content	0.0 mg		
Mercury-free	Yes		
Design / version	Clear		
Show WEEE picto	Yes		
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/In preparation		

Capabilities

Dimmable	Yes
----------	-----

Certificates & standards

Energy efficiency class	A++
Energy consumption	5 kWh/1000h

Country-specific categorizations

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075287822	Folding carton box 1	39 mm x 39 mm x 109 mm	27.00 g	0.17 dm ³
4058075287839	Shipping carton box 10	205 mm x 87 mm x 123 mm	318.00 g	2.19 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.