



Part Number : [1200990005](#)
Product Description : PROFIBUS Receptacle, 5 Poles, Female (Straight) to Lead, 1.0m (3.28') Length
Series Number : 120099
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : BR5U70PP4M0103



Documents & Resources

Drawings
[1200990005_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120099
Description	PROFIBUS Receptacle, 5 Poles, Female (Straight) to Lead, 1.0m (3.28") Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	PROFIBUS Data Line
Type	Single Ended (pigtail)
UPC	78678850807

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	1.0m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16
Orientation	Straight
Panel Mount	Back
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	24

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Mar 27, 2025