



HIGH IMPACT, PRECISION FULL COLOUR THAT LASTS

BRADYJET J4000

Colour
Label Printer

Create a safer, more efficient workplace with compliant, photo-quality full-colour labels, signs and procedures that last. Balance the complexity of safety and compliance labels with the demands of an industrial environment while reducing your safety signage inventory and material waste.

- ▶ **Create compliant labels and signs:** Trust your regulatory and technical standard driven labelling offers the colours needed for ISO, CLP/GHS, ANSI, BS5609 and arc flash
- ▶ **Extend label performance:** Rely on specially formulated materials and ink designed to stand up to harsh environments
- ▶ **Maximise impact, improve efficiency and reduce waste:** Stock and print only what you need, when you need it, in photo-quality full-colour every time





Specifications

Software and Connectivity	
Connectivity Options	USB Ethernet
Software Compatibility	Brady Workstation Windows based driver for 3rd party software use
User Interface Type	PC
Operating System	Windows® 7 Windows® 8 Windows® 10
Physical/Operational Characteristics	
Dimensions	438.15 mm (W) x 231.14 mm (H) x 438.15 mm (D)
Weight (kg)	16
Printer Features	
Recommended Usage per Day	5000
Print Technology	Inkjet
Colour Capability	Full Colour
Print Resolution (dpi)	4800
Max. Print Width (mm)	203.20
Max. Label Width (mm)	203.20
Max. Print Length (mm)	609.60
Media Format	Media on Roll and Ink in Cartridge, supplied separately
Print Speed (mm/sec)	114.30
Includes	(1) BradyJet J4000 Printer (1) Power Cord (1) CMY Ink Cartridge with built in Printhead (1) Pack of 2 Ink Cartridge Storage Caps (1) Media starter roll 101.60 mm wide B-2595 Vinyl (1) USB Cord (1) USB Flash Drive with product information (1) Brady Workstation Basic Suite
Display	LED

Printers

Article No.	Order Ref.	Description
152710	J4000-US	BradyJet J4000 Colour Label Printer
152711	J4000-EU	BradyJet J4000 Colour Label Printer
152712	J4000-UK	BradyJet J4000 Colour Label Printer
322923	J4000-EU-BWS	BradyJet J4000 Colour Label Printer EU + Brady Workstation Suite
322924	J4000-UK-BWS	BradyJet J4000 Colour Label Printer UK + Brady Workstation Suite
322925	J4000-US-BWS	BradyJet J4000 Colour Label Printer US + Brady Workstation Suite



Ensure labels for all your lab samples and equipment are crisp, clear, readable and contain all necessary information. Easily design and create labels for your cryovials, centrifuge tubes, bottles, conicals, slides and other samples in your laboratory.
Workstation.BradyID.com/LAB



Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data.
Workstation.BradyID.com/ProductandWire



Keep your facility safe and compliant by creating custom signs, label and pipemarkers, adding visual safety guidance.
Workstation.BradyID.com/SafetyAndFacility

Ink and storage caps

Article No.	Order Ref.	Description
152713	J40-CAP	J4000 Ink Cartridge Storage Caps
152714	J40-CMY	BradyJet J4000 Full Colour Ink Cartridge



Learn more at
www.bradyeurope.com/J4000



B-7425J chemically resistant polypropylene material

This polypropylene material is ideal for GHS and other full-colour identification applications where resistance to harsh chemicals is required.

Article No.	Order Ref.	Dimensions	Quantity
152778	J40-260-7425J	55.12 mm (W) x 85.09 mm (H)	340
152779	J40-262-7425J	104.90 mm (W) x 154.94 mm (H)	200
152780	J40-265-7425J	177.80 mm (W) x 254.00 mm (H)	100
152781	J40-321-2475J	203.20 mm (W) x 133.35 mm (H)	100
152782	J40-268-2475J	203.20 mm (W) x 279.40 mm (H)	100
152783	J40C-2250-7425J	57.15 mm (W) x 30.48 m (L)	1
152784	J40C-4000-7425J	101.60 mm (W) x 30.48 m (L)	1
152785	J40C-6000-7425J	152.40 mm (W) x 30.48 m (L)	1
152786	J40C-8000-7425J	203.20 mm (W) x 30.48 m (L)	1

B-2595 vinyl material

Ideal for indoor facility labels, including 5S labels, safety labels, warning labels, pipe markers, equipment labels and visual workplace labels.

Article No.	Order Ref.	Dimensions	Quantity
148651	J50-262-2595	104.90 mm (W) x 154.94 mm (H)	200
148653	J50C-4000-2595	101.60 mm (W) x 30.48 m (L)	1
148656	J50C-2250-2595	57.15 mm (W) x 30.48 m (L)	1
148657	J50-260-2595	55.12 mm (W) x 85.09 mm (H)	340
148659	J50-265-2595	177.80 mm (W) x 254.00 mm (H)	100
148660	J50-261-2595	74.93 mm (W) x 109.98 mm (H)	270
148663	J50C-8000-2595	203.20 mm (W) x 30.48 m (L)	1
148664	J50-267-2595	154.94 mm (W) x 210.82 mm (H)	120
148666	J50C-6000-2595	152.40 mm (W) x 30.48 m (L)	1

B-2585 BS5609 polypropylene labels

The material is ideal for international container labelling and yields vibrant, full colour prints and graphics. BS5609 compliant for marine environments.

Article No.	Order Ref.	Dimensions	Quantity
150753	J50-260-2585	55.12 mm (W) x 85.09 mm (H)	340
150754	J50-261-2585	74.93 mm (W) x 109.98 mm (H)	270
150755	J50-262-2585	104.90 mm (W) x 154.94 mm (H)	200
150756	J50-267-2585	154.94 mm (W) x 210.82 mm (H)	120
150757	J50-268-2585	203.20 mm (W) x 279.40 mm (H)	100
150760	J50C-2250-2585	57.15 mm (W) x 30.48 m (L)	1
150761	J50C-4000-2585	101.60 mm (W) x 30.48 m (L)	1
150762	J50C-6000-2585	152.40 mm (W) x 30.48 m (L)	1
150763	J50C-8000-2585	203.20 mm (W) x 30.48 m (L)	1

B-2569 polyester material

Ideal for indoor facility labels, including 5S labels, safety labels, warning labels, pipe markers, equipment labels and visual workplace labels on stainless steel and smooth surfaces.

Article No.	Order Ref.	Dimensions	Quantity
148652	J50C-6000-2569	152.40 mm (W) x 30.48 m (L)	1
148654	J50-262-2569	104.90 mm (W) x 154.94 mm (H)	200
148655	J50C-8000-2569	203.20 mm (W) x 30.48 m (L)	1
148658	J50C-4000-2569	101.60 mm (W) x 30.48 m (L)	1
148661	J50-261-2569	74.93 mm (W) x 109.98 mm (H)	270
148662	J50-260-2569	55.12 mm (W) x 85.09 mm (H)	340
148665	J50C-2250-2569	57.15 mm (W) x 30.48 m (L)	1
148667	J50-265-2569	177.80 mm (W) x 254.00 mm (H)	100
148668	J50-267-2569	154.94 mm (W) x 210.82 mm (H)	120

B-2475 polyester material

Ideal for product labelling, logos, Right to Know labels and barcode applications. UL approved.

Article No.	Order Ref.	Dimensions	Quantity
152802	J40-136-2475	38.10 mm (W) x 19.05 mm (H)	1000
152803	J40-235-2475	38.10 mm (W) x 25.40 mm (H)	750
152804	J40-137-2475	50.80 mm (W) x 25.40 mm (H)	750
152805	J40-18-2475	76.20 mm (W) x 25.40 mm (H)	750
152806	J40-19-2475	76.20 mm (W) x 50.80 mm (H)	250
152807	J40-55-2475	101.60 mm (W) x 50.80 mm (H)	250
152808	J40-25-2475	101.60 mm (W) x 152.40 mm (H)	80
152809	J40C-1125-2475	28.58 mm (W) x 30.48 m (L)	1
152810	J40C-2250-2475	57.15 mm (W) x 30.48 m (L)	1
152811	J40C-4000-2475	101.60 mm (W) x 30.48 m (L)	1
152812	J40C-8000-2475	203.20 mm (W) x 30.48 m (L)	1

B-2581 repositionable vinyl material

The material can be printed in full colour at your premises when you need them and they are designed for frequent repositioning.

Article No.	Order Ref.	Dimensions	Quantity
151110	J50C-2250-2581	57.15 mm (W) x 30.48 m (L)	1
151111	J50C-4000-2581	101.60 mm (W) x 30.48 m (L)	1
151112	J50C-6000-2581	152.40 mm (W) x 30.48 m (L)	1
151113	J50C-8000-2581	203.20 mm (W) x 30.48 m (L)	1

