

Individually tested premium nitrile gloves, for advanced, high-risk chemical protection

- **Assured quality:** Produced in an ISO 9001-certified facility, AlphaTec® 37-900 nitrile-coated gloves are subject to 100% sampling inspections before dispatch, including leak-proof air pressure tests and defect checks
- **Advanced protection:** Made with an advanced nitrile formulation, these reusable industrial gloves provide superb chemical protection and exceptional permeation and abrasion resistance
- **Enhanced grip:** Both robust and comfortable, these chemical-resistant gloves also feature a reverse lozenge finish, for excellent grip performance in both wet and dry work environments

Industries

- Automotive
- Machinery and Equipment

Applications

- Delivery of parts to production line
- Painting or cleaning tools or robots
- Changing tools and dies



Previously known as: Solvex® 37-900

Key Features

- **100% sampling inspection*:** For assured handling of hazardous chemicals
- **Highly advanced nitrile film:** Truly superior abrasion resistance
- **Reverse lozenge finish:** Excellent grip performance

*including a leak-proof air pressure test and defect checks

Vulcanization Chemical Accelerators

- Mercaptobenzothiazole
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



0493

EN388: 2016



4101X



ISO 18889

EN ISO 374-1:2016
Type A



AJKLOPT

EN ISO 374-5



VIRUS



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® Solvex® 37-900	Liner Material: Flocked Coating Material: Nitrile	7, 8, 9, 10, 11	380 / 15	Red	• 12 pairs per bag, 6 bags per carton • Vend pack variant , 1 pair per inner bag , 72 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.