



Part Number : [190700042](#)

Product Description : InsulKrimp Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 5-6 (M3-3.5), Length 20.50mm, Red, Tape

Series Number : 19070

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : AA-232-06XT



Documents & Resources

Drawings

[190700042_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-009-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19070
Description	InsulKrimp Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 5-6 (M3-3.5), Length 20.50mm, Red, Tape
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753069046

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin

Net Weight	0.546/g
Packaging Type	Adhesive Tape on Reel
Stud Size	5-6 (M3-3.5)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.70mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.35-0.80

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880023</u>
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	<u>638851300</u>