

IN 19 LK 14-140

Screwdriver bit socket 1/2"

with ball end, for in-hex screws, long pattern

| | |
|-----------------------|-------------|
| Code | ETIM |
| 1936328 | EC002157 |
| EAN | UNSPSC |
| 4010886864203 | 27-11-17-01 |
| Country of origin | eCl@ss |
| Germany | 21-04-04-02 |
| Customs tariff number | |
| 82079030 | |



Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- Total swivel angle approx. 15-20°

Article information

| | | | |
|--|-----------------------|--------------------------------------|-------------------------------|
| Contents (Qty of pieces) | 1 | Drive connector square female [inch] | 1/2" |
| Net weight [kg] | 0,225 kg | Standard | DIN 3120 - C 12,5 ISO 1174 |
| Total length [mm] | 140 mm | Width across flats 1 [mm] | 14 |
| Total width [mm] | 24,7 mm | Backup | Ball Catching Cricket |
| Surface | chrome-plated | Tip length | 100,0 mm |
| Material | Chrome-vanadium steel | Insert Ø Actuator | 24,7 mm |
| Drive connector square female (metric) | 12,5 mm | Total swivel angle | 15 - 20° |