

Features

- This hose comes supplied with a male coupling ready assembled for direct connection to a pump or cylinder.
- 700bar working pressure.
- 2 m long with coupling, easy to connect.
- Durable, high quality
- Dust Cap on NPT 3/8 Connector included.

RS PRO 2000mm PU Hydraulic Hose Assembly, 700bar Max Pressure

RS Stock No.: 0291727



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Thermoplastic hydraulic hoses for use in demanding environments and applications. The hoses come supplied with a male coupling ready assembled for direct connection to a pump or cylinder and have a maximum working pressure of 700bar. Durable glass-filled nylon reservoir and nylon encapsulating aluminium pump base for maximum corrosion resistance 2.0m safety hose.

- Four layers design, including 2 high strength steel wire braids.
- Outside jacket is polyurethane, for maximum abrasion resistance.
- Crimped on rubber strain relief for improved life and durability.
- Dust caps to protect connections when not in use.

Note

Working pressure quoted is the maximum acceptable system pressure.

- All fittings and valves are 700bar pressure-rated and have 3/8 - 18 NPT threads.

General Specifications

Model	0291727
Max. Operating Pressure	700Bar
Overall Length	2 m
Inside Diameter	6.4 mm
Cover Material	PU
Inner Hose Material	Thermoplastic
Connector A	NPT 3/8 Male
Connector A Angle	Straight
Connector B Thread Size	3/8in
Connector B Gender	Male

Approvals

Compliance/Certifications	CE, EN ISO 12100:2010, EN 809:1998+A1:2009
Declarations	UKCA