Features

- Start, Reset, Pause Input
- 6 Digits (PV) Display
- 24Vac/dc Power Supply
- 72X72mm Panel Dimension
- Relay Output 5A@250Vac

RS PRO Digital Timer

RS Stock No:874210



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Timer:

- Start, Reset and Pause Input
- Programmable Time Bases (Second, Minute, Hour)
- Operation with Automatic and Manuel Reset
- NPN/PNP Type Operation
- Relay Output (5A@250Vac)

General Specifications

Supply Voltage and Power	24Vac/dc 50/60Hz
Sensor Inputs	Start, Reset and Pause Input
Output	Relay Output (5A@250Vac)

Mechanical Specifications

Dimension	72 mm x 72 mm 87,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

