



### Main

Range of product	Mita
Product name	Cableline 40
Product or component type	Internal corner
Colour tint	White
Quantity per set	Set of 1

### Complementary

Fixing mode	By screws extra security
Material	UPVC (unplasticized polyvinyl chloride)

### Environment

Ambient air temperature for operation	-5...60 °C
---------------------------------------	------------

### Packing Units

Package 1 Weight	1.000 G
Package 1 Height	1.000 Mm
Package 1 width	1.000 Mm
Package 1 Length	1.000 Mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------