

RATCHETING COMBINATION SPANNER METRIC RS 14MM



- A ratcheting ring and open ended spanner combined with the same size at each end
- Simply turn over to reverse the direction of use when ratcheting
- TengTools hip grip design on the ring end for contact with the flat side of the fastening
- 72 teeth ratchet spanners giving a 5° increment between clicks
- Ideal for rapid tightening and loosening of fastenings
- Chrome vanadium satin finish
- Designed and manufactured to DIN ISO 1711-1 and DIN 3113A

Ratcheting Combination Spanner 14mm

General information

Country of origin: Taiwan
Barcode: 5020385043619
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002218
UNSPSC: 27111705

Dimensions

Net weight (g): 112
Length: 182 mm

Attributes

Product type: Combination Spanners
Material: CrV
Certificates: N/A
Size: 14 mm
Number of teeth: 72
Reverse direction: Turn over
Flexible head: No
Tethering facility: No
Spanner type: Regular
Ratcheting: Yes
Unit of measurement: Metric
Jaw diameter: 30.8
Jaw height (mm): 6.2
Offset angle jaw (°): 15
Ring diameter (mm): 27.0
Ring height (mm): 9.3

Features



Technical changes and errors may occur. 01-08-2024 19:49



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås, Sweden