
# Parker Product Datasheet



Quick coupling system with nominal diameter 7,4 for breathing air applications up to 35 bar. Especially developed for the area of breathing air protection. Available made of brass.

**PART NUMBER:** 95KSTF06BPN
**COUPLING HALF:** Coupler
**CONNECTION SIZE:** 6 MM
**CONNECTION TYPE:** Hose Barb
**BODY MATERIAL:** Brass
**FUNCTION:** Safety (Single Shut-Off)

## PRODUCT OVERVIEW

Parker's coupling system has been developed specifically for the area of breathing protection. Coupling system with single-hand operation. The used UltraFlo valve guarantees optimum flow and low pressure drop. Coupling system with additional safety locking system, this safety lock prevents unintentional disconnection. To disconnect, the plug must first be pushed further into the coupling before it can be unlocked. Profile 95 cannot be interconnected with the 96 series. Tested according EN 139 standard.

Markets:
- Life Science
- Rescue Equipment

Features/Benefits:
- Interchangeable to the most common profiles for breathing air applications
- UltraFlo valve for optimum flow and low pressure drop

- Additional safety locking system to prevent unintentional disconnection
- Tested according EN 139 standard
- Single-hand operation for easy and fast connection

Applications:
- Breathing Air

# TECH SPECIFICATIONS

| | |
|---|---|
| **DIAMETER** | 7.4 mm (nominal) |
| **DIVISION** | Low Pressure Connectors Europe Division |
| **FOR FLUID TYPE** | Oxygen (Breathing air, medical, industral oxygen) |
| **WEIGHT** | 0.1 kg |
| **PRODUCT SERIES** | Series 95 |
| **INTERCHANGE TYPE** | Parker Profile |
| **COMPATIBLE FITTING** | Plug |
| **TECHNOLOGY** | Pneumatics |
| **PLATING TYPE** | Nickel-Plated |
| **INDUSTRY** | Rescue Equipment |
| **HEX SIZE** | 19 mm |
| **FUNCTION** | Safety (Single Shut-Off) |
| **DIVISION** | Low Pressure Connectors Europe Division |
| **SEAL MATERIAL** | NBR |
| **MINIMUM OPERATING TEMPERATURE** | -20 °C |
| **VALVE INCLUDED** | Yes |
| **PRODUCT STYLE** | Quick Connect |
| **OPERATION TYPE** | Sleeve |
| **PRODUCT TYPE** | Pneumatic Quick Couplings |

| | |
|---|---|
| **LENGTH** | 74 mm |
| **BRAND** | Parker |
| **QUANTITY PER BOX** | VLOOKUP(A481,[1]default_1!$A:$P,16,FALSE) |
| **CONNECTION TYPE** | Hose Barb |
| **CONNECTION SIZE** | 6 mm |
| **MAXIMUM OPERATING TEMPERATURE** | 212 °F |
| **MAXIMUM OPERATING TEMPERATURE** | 100 °C |
| **REGION OF ORIGIN** | Germany |
| **APPLICATION** | Breathing Air |
| **MINIMUM OPERATING TEMPERATURE** | -4 °F |
| **BRAND** | Rectus |
| **OUTSIDE DIAMETER** | 23 mm |
| **SLEEVE TYPE** | Standard Sleeve |
| **SLEEVE MATERIAL** | Brass |
| **MAXIMUM OPERATING PRESSURE** | 508 psi |
| **FLOW RATE** | 1700 L/min (air) |
| **COUPLING HALF** | Coupler |
| **BODY MATERIAL** | Brass |
| **VALVE TYPE** | High Flow Valve |
| **MAXIMUM OPERATING PRESSURE** | 35 bar |
| **INDUSTRY** | Life Science |