

Price* : 37.26 GBP



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	20 W
Input voltage	110...250 V AC 50/60 Hz
Electrical connection	4 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	UL VDE
Material	Extruded aluminium for body Plastic for cover
Height	External: 98 mm
Width	External: 38 mm
Depth	External: 75 mm
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
