

## Datasheet

## RS PRO ispot Blade LED Desk Lamp

### Description

The ispot Blade Desk Lamp incorporates innovative and minimalistic modern design. It boasts an attractive ultra-thin design with a 180 degree tilting head. The ispot blade includes a touch control interface to control the colour temperature and brightness.

Available in a Black or White finish.



### Range

### RS Stock No

RS PRO ispot Blade 8W 3000-6500K  
Black

111-9984

RS PRO ispot Blade 8W 3000-6500K  
White

111-9990

### Technical Specification

Voltage	220-240VAC~ 50/60Hz
Lamp	SMD LED
Colour temp.	5700K (Daylight)
IP rating	IP54

### Features

- LED desk lamp – 8W
- Warm White (3000K) – Daylight (6500K)
- Touch control interface
- 180 degree adjustable head
- Available in Black and White finishes
- 30000 hours rated life

### Dimensions (mm), Beam Angle & Lumens

RS Stock No.	Lumen Output	Wattage	Dimensions (mm)
111-9984	480 lm	8W	270x140x330
111-9990	480 lm	8W	270x140x330

### Standards

- BS EN 60598-1+A11
- BS EN 60598-2-1
- BS EN 60598-2-5
- BS EN 62471
- BS EN 62493
- BS EN 55015+A2
- BS EN 61547
- BS EN 61000-3-2+A2
- BS EN 61000-3-3