

Engraving plate - GPK/SK296X200X0.8 BU/WH - 0826835

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Engraving plate, Plate, blue/white, unlabeled, can be labeled with: Engraving, Mounting type: Adhesive, Lettering field: 296 x 200 mm

The illustration shows various versions of the article



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 362436
Weight per Piece (excluding packing)	58.55 g
Custom tariff number	39203000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	296 mm
Height	0.8 mm
Width (a)	200 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.

General

Color	blue/white
Material	TRANSPLY-ABS
Adhesive	Acrylic
Printability	Engraving
	Plotter
Device	5144615 CMS-P1-PLOTTER

Engraving plate - GPK/SK296X200X0.8 BU/WH - 0826835

Technical data

General

	5145546 P1 ENGRAVING UNIT
Adhesive strength	50 µm
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410