



FLAME HIGH VIS BIB'N'BRACE CLASS 2 1584 FLAM

ART. NO: 126510

Front placket opening with two-way, full-length front zip and concealed snap fastening / 2 CORDURA® reinforced chest pockets with flap and concealed snap fastening, 1 with D-ring / 2 front pockets / Double reinforced crotch seam / 2 CORDURA® reinforced back pockets with flap and concealed snap fastening / Hammer loop / CORDURA® reinforced folding rule pocket with flap and concealed snap fastening, pen pocket and button and loop for sheath knife / Leg pocket with flap and concealed snap fastening, mobile phone pocket with flap and velcro fastening / Aramide-reinforced thigh panels / Aramide-reinforced knee pockets with inside opening / Height adjustment for knee pads in knee pocket / CORDURA®-reinforced leg ends / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 8 cal/cm² (see Electric arc table for certified garment combinations for EN 61482-1-2 class 2 and open arc according to EN 61482-1-1), EN ISO 11612 A1 B1 C1 E2 F1, EN ISO 11611 A1 class 1 (see Flame and welding table for certified garment combinations for EN 11612 C2, E3, F2 and EN 11611 A1 class 2), EN 1149-5, EN ISO 20471 class 2 and EN 14404 together with kneepads 124292 / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: 75% cotton, 24% polyester, 1% anti-static fibre. Reinforcement: 74% cotton, 25% para-aramid, 1% anti-static fibre. CORDURA® reinforcement: 79% cotton FR, 20% polyamide, 1% antistatic fibre. In transition to PFAS free.

Weight: 365 g/m². Reinforcement 340 g/m².

Color: F171 High vis Yellow/Navy

Size: Tall: C146-C158 Regular: C44-C64 Short: D84-D120



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04