

**ENGLISH** 

#### **Datasheet**

# RS Pro Straight 75 $\Omega$ Cable Mount BNC Connector, jack, Clamp Termination RG59 Silver

RS Stock No: 546-4437



#### **Product Details**

RS Pro cable mount BNC connector has a silver plated body, silver plated centre contact and is suitable for RG59 cables. This 75  $\Omega$  straight BNC connector comes with cable jack, clamp termination.

#### **Features and Benefits**

- Silver plated body
- Silver plated centre contact
- Jack, clamp termination



## ENGLISH

### **Specifications:**

•	
Body Orientation	Straight
Body Plating	Silver
Cable Type	RG59
Contact Material	Copper
Contact Plating	Silver
Gender	Female
Impedance	75 Ω
Mounting Type	Cable Mount
Operating Frequency	1 GHz
Polarity	Normal
Termination Method	Clamp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-65 to +165°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)