

MLFB-Ordering data

6SE6400-2FS01-0AB0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	Connections
------------	-------------

Input	
Number of phases	1 AC
Line voltage	200 ... 240 V
Output	
Rated current	10.0 A

Line side	
Version	screw-type terminal
Conductor cross-section	1,0 ... 2,5 mm ²
Load side	
Version	Pigtail
Cable length	0.37 m

Mechanical data

Dimensions	
Width	73.0 mm
Height	200.0 mm
Depth	43.5 mm
Degree of protection	IP20 / UL open type
Net weight	0.5 kg

PE connection	
Version	M4 stud

Standards

Compliance with standards	CE / UL
---------------------------	---------