



# Product data sheet

Power tools for trade & industry

Cordless Hydraulic Cutting Tool

## PRO GKH 18V-50



18V Hydraulic Cable Cutter with Outstanding Maintenance Interval and Intelligent Cutting Detection

### The most important data

Max. capacity cable diameter	40 mm
Cu- and Al-cables (multi and fine stranded)	Yes
Head rotation	360 °

**Order number** 0 601 9P0 000

## Technical data

### Additional data

Max. capacity cable diameter	40 mm
Cu- and Al-cables (multi and fine stranded)	Yes
Head rotation	360 °
Cutting force max	50 kN
Automatic retraction	Yes
Intelligent cutting detection	Yes
Maintenance interval	20.000 cycles
Manual pressure release	Yes
Manual retraction stop	Yes
USB connector	Yes
Steel Cable (ACSR)	No
Read-Out Functionality	Yes
Work light	Yes
Automatic pressure limitation and monitoring	Yes
USB mode	USB 2.0
Cutting time	2 s to 5 s (depending on cable cross-section)



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Strong, reliable performance with clean cuts thanks to special blades and electronic pressure monitoring
- Long lifetime with outstanding maintenance intervals needed only after 20,000 cuts
- Efficient cutting thanks to intelligent cutting detection which opens jaws automatically after each cut
- Comfortable to use thanks to ergonomic design, 360-degree rotatable head, and optimized center-of-gravity
- Convenient overview of tool's cutting history, important parameters, and maintenance intervals, through USB connection and read-out software

**HEAVY  
DUTY**