

Datasheet

RS Pro M12 316, A4 Plain Stainless Steel Dome Nut

RS Stock No: **248-4523**



Product Details

RS Pro dome nut made of type-316, A4 grade stainless steel offers corrosion resistance. This dome nut features M12 metric threading to cover the end of the projecting screw thread. The nut meets all the requirements of DIN6923 standards.

Features and Benefits

- 316 A4 stainless steel construction
- M12 metric threading
- Hide or cover the end of a projecting screw thread
- Meet the requirements of DIN6923 standards



Specifications:

Finish	Plain
Material	Stainless Steel
Overall Height	22 mm
Stainless Steel Type	316, A4
Thread Size	M12
Specification	DIN 1587
Thread Pitch	1.75
Width Across Corners	21.1 mm
Width Across Flats	19 mm
Wrenching Height	10 mm