

**ZMA20/38** **Precision locknut**

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information**Main Dimensions & Performance Data**

d	M20X1	Thread
D	38 mm	Outside diameter
h	20 mm	Height
M _A	3 Nm	Mounting torque set screw
F _{aB}	174,000 N	Breaking load, axial
M _L	40 Nm	Breakawag
M _{AL}	18 Nm	Mounting torque reference
M _M	0.297 kg*cm ²	Mass moment of inertia
≈m	0.119 kg	Weight

Dimensions

d ₁	33 mm	Plant diameter outside
t	2 mm	Hight retaining slot
b	5 mm	Width retaining slot
c	10 mm	Distance bore
m	M5	Threaded - threaded pin