

Datasheet

RS Pro Asymmetric HID Floodlight SON-T 400 W 230 V ac, IP65, Aluminium

RS Stock No: **237-265**



Product Details

RS Pro 400 W asymmetric HID floodlight features high quality die cast body for durability. The asymmetric high purity anodised reflector improves light levels or increases spacing distances between multiple floodlights. It includes mounting bracket. The asymmetric HID floodlight meets EN60598 standards.

Features and Benefits

- High quality die cast body
- Asymmetric high purity anodised reflector improves light levels or increases spacing distances between multiple floodlights
- No upward light pollution when angled correctly
- Toughened hinged front glass with aluminium fastening clips
- Includes mounting bracket



ENGLISH

Specifications:

Case Material	Aluminium
Depth	140 mm
Dimensions	420 x 400 x 140 mm
Height	420 mm
IP Rating	IP65
Lamp Type	SON-T
Reflector Shape	Asymmetric
Standards Met	CE Certified; BS EN 60598
Voltage Rating	230 V ac
Wattage	400 W
Width	400 mm