



□□□□

辅助接触器，44E，DIN EN 50011， 4 NO + 4 NC，螺栓型端子连接 AC 运行 220V AC 50/60Hz

产品名称	辅助接触器
产品类型名称	3TH4
接触器的结构尺寸	0
参考标示 符合 IEC 81346-2:2009	K
RoHS 指令（日期）	12/31/2099
环境温度 运行期间	-25 ... +55 °C
电压类型 控制馈电电压的	AC
控制馈电电压 AC 时	
• 50 Hz 时 测定值	220 V
• 60 Hz 时 测定值	220 V
控制馈电电压频率	
• 1 测定值	50 Hz
• 2 测定值	60 Hz
常闭触点数量 用于辅助触点	4
• 延迟转换的	0
• 滞后转换的	0
• 相交式的转换	0
常开触点数量 用于辅助触点	4
• 延迟转换的	0
• 超前转换的	0
• 相交式的转换	0
转换器数量 用于辅助触点	0
控制元件的编码数字和编码字母	44 E
工作电流 AC-15 时	
• 230 V时 测定值	10 A
• 400 V 时 测定值	6 A
紧固类型	按照DIN EN 50022在35mm安装导轨上的螺丝固紧和扣接固紧
高度	78 mm
宽度	45 mm
深度	102 mm
电气连接规格 用于辅助和控制电路	螺栓连接
安全	
B10 值 需求率较高 符合 SN 31920	1 000 000; 0.3 x Ie 时
IEC 61508	



T1 值	
• 用于检测试验间隔时间或使用时间 符合 IEC 61508	20 a
电气安全	
防护等级 IP 正面的 符合 IEC 60529	IP00; 螺栓拧紧时 IP20, 有未使用的触点时同样
认可 证书	

General Product Approval					Functional Safety
					Type Examination Certificate

Test Certificates				other	Railway
Special Test Certificate	Miscellaneous	Type Test Certificates/Test Report	Miscellaneous	Confirmation	Special Test Certificate

Environment
Environmental Confirmations

更多信息
包装信息 https://support.industry.siemens.com/cs/cn/zh/view/109813875
Information- and Downloadcenter (产品目录, 产品介绍册, ...) https://www.siemens.com/ic10
Industry Mall (网上订购系统) https://mall.industry.siemens.com/mall/zh/zh/Catalog/product?mlfb=3TH4244-0AN2
Cax 在线发生器 http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TH4244-0AN2
Service&Support (用户手册, 操作说明书, 认证证书, 特性曲线, 常见问题,...) https://support.industry.siemens.com/cs/ww/zh/ps/3TH4244-0AN2
图片数据库 (产品照片, 2D比例图, 3D模型, 设备电路图, EPLAN Makros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TH4244-0AN2&lang=en
特性曲线: 脱扣特征, I _t , 允通电流 https://support.industry.siemens.com/cs/ww/en/ps/3TH4244-0AN2/char
其他特性曲线 (如电气寿命, 开关频率) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TH4244-0AN2&objecttype=14&gridview=view1



上一次修改:

2023/12/20 