

FEATURES

- IP66 ingress protection by use of Neoprene O-Ring continuous seal
- Cover seal temperature stability -40 to +100°C
- DIN rail mounting point
- Lid and base joined using captive stainless steel lid screws
- Wall thickness 3mm

RS PRO General Purpose Enclosures -Unpainted Die Cast Aluminium Enclosure

RS Stock No.: 8462973



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

General Purpose Enclosures



Product Description

IP66 Diecast Aluminium Enclosure, Natural Finish

A watertight series of enclosures that are manufactured from diecast aluminium (ALSi12). The enclosures are IP66 rated and are specifically designed for Harsh & Demanding applications. The enclosure includes a lid and base, captive stainless steel lid screws, a Neoprene O-Ring continuous gasket and 4 copper plated earthing screws for grounding. These high standard enclosures are suitable for use in a wide range of environments including indoors and outdoors, providing excellent protection of internal electrical components in a range of applications.

General Specifications

Body Material	Die Cast Aluminium			
Colour	Unpainted			
Lid Colour	Unpainted			
Handheld	No			
Flanged	No			
Shielded	No			
Transparent Door	No			
Features	Cover seal temperature stability -40 to +100°C			

Mechanical Specifications

Gasket Material	Neoprene
External Length	330 mm
External Height	180 mm
External Width	230 mm
External Dimension	330 x 230 x 180mm

Protection Category

IP Rating	IP66



Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Similar Products

Stock No.	Brand	Product Name	Body Material	Colour	Shielded
8462960	RS PRO	Die Cast Aluminium Enclosure	Die Cast Aluminium	Unpainted	No
8462970	RS PRO	Die Cast Aluminium Enclosure	Die Cast Aluminium	Unpainted	No

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws

