



Product data sheet

Power tools for trade & industry

Straight Grinder

PRO GGS 30 S



Powerful, versatile, safe: the high-performance grinder for all grinding tasks

The most important data

Rated input power	650 W
No-load speed	7,000 – 33,000 rpm
Weight	1.5 kg

Part Number 0 601 2B5 160

Technical data

Technical data

No-load speed	7,000 – 33,000 rpm
Rated input power	650 W
Power output	400 W
Spindle collar diameter	43 mm
Weight	1.5 kg
Max. collet diameter	6 mm, 1/4", 3 mm, 8 mm
Max. grinding tool diameter	25 mm
Spanner size of locking nut	17 mm
Spanner size of grinding spindle	17 mm
Max. polishing tool diameter	45 mm
Switch	Lockable Switch
Packaging dimensions (width x length x height)	118 x 358 x 138 mm
Voltage, electrical	110 V
Collet diameter supplied	6 mm

Noise/vibration information

Surface grinding (roughing with grinding tool diameter of 25 mm)

Vibration emission value ah	3 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High efficiency thanks to powerful 750 W motor
- Precision work thanks to speed dial and constant speed control functions
- Easy and convenient accessory change with handy spindle lock function
- Increased user protection with KickBack Control, soft start, and restart protection
- Ergonomic design with compact, comfortable grip size

**HEAVY
DUTY**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

